

Product data sheet

Characteristics

E3032V1PR_FGGS

2Gang 1Way Vert. Press On/off Switch w/ Green
Fluorescent Indicator, Grey Silver



Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Flush Surface
Switch function	Momentary
Switch application	Switch
Bulb type	Fluorescent with green
Colour tint	Grey silver

Complementary

Rated current	100 mA, 24 V, DC
Number of gangs	2 gangs vertical
Material	Brass terminals Polycarbonate plastic part
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23 mm
Depth	36 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Contractual warranty

Warranty period	18 months
-----------------	-----------