



Main

Range of product	Neo C-Metro
Product or component type	TV/FM socket
Socket number	2
Colour tint	White

Complementary

Wiring device mounting	Flush Surface
Material	Brass metal parts Polycarbonate plastic part Steel metal parts
Bandwidth	125...862 MHz TV 5...68 MHz TV 87.5...108 MHz FM
Insertion loss	3.5 dB +/- 0.5 dB
Connections - terminals	Saddle terminal Screw with pressure plate
Width	87 mm
Height	87 mm
Depth	24.9 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	BS 3041

Contractual warranty

Warranty period	18 months
-----------------	-----------