

Product data sheet

Specifications



750ohm TV-FM Socket Outlets with 2 Cord Grips, Master, White

E3032VTVFM-2_WW

⚠ Discontinued on: Dec 7, 2018

⚠ Discontinued

Main

Range Of Product	Neo C-Metro
Product Or Component Type	TV/FM socket
Socket Number	2
Colour Tint	White

Complementary

Wiring Device Mounting	Surface Flush
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Bandwidth	125...862 MHz TV 5...68 MHz TV 87.5...108 MHz FM
Maximum Insertion Loss	3.5 dB +/- 0.5 dB
Connections - Terminals	Saddle terminal Screw with pressure plate
Width	87 mm
Height	87 mm
Depth	24.9 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	BS 3041

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications