



Main

Range of product	Neo ELV+
Product or component type	Courtesy panel
Device application	Control
Number of channels	3
Additional information	5 or 12 V DC selectable
Colour	Silver

Complementary

Connector type	RJ45 5e
Output type	Voltage free dry contact
Rated current	20 mA < 24 V DC
Status LED	LED amber butler call LED amber do not disturb LED amber make up room
Number of gangs	3 gangs horizontal
Width	87 mm
Height	87 mm
Embedding depth	20.3 mm
Depth	35 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %

Contractual warranty

Warranty period	18 months
-----------------	-----------