



Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Flush Surface
Switch function	Momentary
Switch application	Switch
Bulb type	Fluorescent with green
Colour tint	Grey silver

Complementary

Rated current	100 mA, 24 V, DC
Number of gangs	3 gangs horizontal
Material	Brass terminals
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23 mm
Depth	36 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.