

Product data sheet

Specifications



10A 3 GANG 1 WAY SWITCH W. LED, WHITE

E3033H1_EWWW_G19

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Neo
Product Or Component Type	Control switch
Wiring Device Mounting	Surface Flush
Switch Function	1-way
Switch Application	Switch
Load Type	Incandescent lamp Fluorescent lamp Resistive Inductive
Bulb Type	LED (white)
Colour Tint	White

Complementary

Rated Current	10 A at 250 V AC 50/60 Hz
Number Of Gangs	3 gangs horizontal
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23.5 mm
Depth	36 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1 EN 60669-1 GB 16915.1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.7 cm
Package 1 Length	3.6 cm
Package 1 Weight	0.001 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations