



### Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Surface Flush
Switch function	1-way
Switch application	Switch
Load type	Resistive Inductive Incandescent lamp Fluorescent lamp
Bulb type	Fluorescent with green
Colour tint	Grey silver

### Complementary

Rated current	10 A, 250 V, AC, 50/60 Hz
Number of gangs	3 gangs horizontal
Material	Brass metal parts Polycarbonate plastic part Steel metal parts
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23.5 mm
Depth	36 mm

## Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	IEC 60669-1 GB 16915.1 EN 60669-1

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------