



Main

Range	Neo ELV+
Product or component type	Switch
Switch application	On/Off switching
Colour tint	Grey silver

Complementary

Connector type	RJ45 for 5e category cables
Output type	Voltage free dry contact
Rated current	20 mA with voltage < 24 V DC
Status LED	Amber LED for on/off indication
Number of gangs	3 gangs with horizontal orientation
Width	87 mm
Height	87 mm
Embedding depth	23.45 mm
Depth	35 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications