

Product data sheet

Specifications



3 Gang Switching Control Wallplate with Amber LED, Grey Silver

E3033LV_EAGS

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Neo ELV+
Product Or Component Type	Switch
Switch Application	On/off switching
Colour Tint	Grey silver

Complementary

Connector Type	RJ45 5e)
Output Type	Voltage free dry contact
Rated Current	20 mA at < 24 V DC
Status Led	LED (amber) on/off indication
Number Of Gangs	3 gangs horizontal
Width	87 mm
Height	87 mm
Embedding Depth	23.45 mm
Depth	35 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.9 cm
Package 1 Width	4.6 cm
Package 1 Length	8.8 cm
Package 1 Weight	113.247 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	15 cm
Package 2 Width	19 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	6 cm
Package 2 Weight	679 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6794.82 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not compliant
