



Main

| | |
|---------------------------|------------------------|
| Range | Neo |
| Product or component type | Control switch |
| Wiring device mounting | Flush Surface |
| Switch function | Momentary |
| Switch application | Switch |
| Bulb type | Fluorescent with white |
| Colour tint | White |

Complementary

| | |
|------------------------------|--|
| Rated current | 100 mA, 24 V, DC, 50/60 Hz |
| Number of gangs | 3 gangs vertical |
| Material | Brass terminals Polycarbonate plastic part |
| Clamping connection capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Embedding depth | 23 mm |
| Depth | 36 mm |

Environment

| | |
|---------------------------------------|------------|
| Ambient air temperature for operation | 0...40 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | Indoor use |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|