

Product data sheet

Specifications



TruGlobal Socket (only available in selected countries), White

E3426-10IS_WW

Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	3P with shutters 2P with shutters
Outlet Standard	IEC 60884
Colour Tint	White

Complementary

Wiring Device Mounting	Surface Flush
Rated Current	10 A at 250 V AC 50/60 Hz
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Load Type	Resistive
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	23 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications