



Main

Product or component type	Power socket-outlet
Outlet poles configuration	3P with shutters
Outlet standard	GB 2099.1
Colour tint	Grey silver

Complementary

Wiring device mounting	Flush Surface
Rated current	10 A, 250 V, AC, 50/60 Hz
Material	Brass with metal parts Nylon with shutter Polycarbonate with plastic part Steel with nut Steel with screws
Load type	Resistive
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	21 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	GB 2099.1

Contractual warranty

Warranty period	18 months
-----------------	-----------