

# Product data sheet

Specifications



## 10A 3 Pin Socket Outlet, Grey Silver

E3426CS\_GS

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	3P with shutters
Outlet Standard	GB 2099.1
Colour Tint	Grey silver

### Complementary

Wiring Device Mounting	Flush Surface
Rated Current	10 A at 250 V AC 50/60 Hz
Material	Brass: metal parts Nylon: shutter Polycarbonate: plastic part Steel: nut Steel: screws
Load Type	Resistive
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	21 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	GB 2099.1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.7 cm
Package 1 Length	2.1 cm
Package 1 Weight	111.667 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------