



Main

Range	Neo
Product or component type	Power socket-outlet
Outlet poles configuration	2P with shutters
Outlet standard	GB 2099.1
Colour tint	White

Complementary

Wiring device mounting	Flush Surface
Rated current	10 A, 250 V, AC, 50/60 Hz
Material	Brass with metal parts Nylon with shutter Polycarbonate with plastic part Steel with metal parts
Load type	Resistive
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	18 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	GB 2099.1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant

 Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations