



### Main

Product or component type	Power socket-outlet
Outlet poles configuration	3P with shutters
Outlet standard	BS 1363 MS 589
Colour tint	Grey silver

### Complementary

Wiring device mounting	Flush Surface
Rated current	13 A, 250 V, AC, 50/60 Hz
Material	Polycarbonate with grid plate Polycarbonate with surround Brass with contact Steel with brass plating with screws Steel with brass plating with terminals
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	18 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	IEC 60884 MS 589 SS 145

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1301 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---