



Main

Range	Neo
Product or component type	Connection unit
Colour tint	White
Standards	BS 5733

Complementary

Wiring device mounting	Flush Surface
Rated current	45 A
Number of cables	1 - cable cross section: 10 mm ² with input 1 - cable cross section: 10 mm ² with output 1 - cable cross section: 6 mm ² with output (flexible)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Contractual warranty

Warranty period	18 months
-----------------	-----------