

# Product data sheet

Specifications



## Wireless, FreeLocate Switch Control Unit, 1 Key, 315MHz, Grey Silver

E3851WTXBC\_GB

⚠ Discontinued on: Jan 1, 2006

⚠ Discontinued

### Main

Range Of Product	Neo-X
Product Or Component Type	Control switch 1-key
Transmission Frequency	315 MHz
Operating Distance	60 m open environment
Number Of Batteries	1 CR2032 lithium
Provided Equipment	User manual Button cell battery 2 screws Wall-mount bracket PC sheet
Colour Tint	Grey silver

### Complementary

Status Led	LED backlight (amber) all off LED backlight (blue) scene LED backlight (red) device
Width	87 mm
Height	87 mm
Depth	14 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Standards	EN 60669-2-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	12.2 cm
Package 1 Length	12.2 cm
Package 1 Weight	93.1 g

### Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months