


# E3SUPS15KHB2

Easy UPS 3S 15 kVA 400 V 3:3 UPS with internal batteries - 25 minutes runtime



## Overview

Description	High-efficiency 3-phase UPS with internal batteries providing a runtime of 25 minutes. The UPS features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 15 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. For battery runtime details, see the runtime charts published under the Documents tab.
Model Name	Easy UPS 3S 15 kVA 400 V 3:3 UPS with internal batteries - 25 minutes runtime
Includes	Dust filter , Installation guide
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Belarus , Belgium , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Central African Republic , Chad , Chile , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominican Republic , Egypt , Equatorial Guinea , Estonia , Ethiopia , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guinea , Guyana , Hong Kong , Hungary , Iceland , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Mauritania , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Niger , Nigeria , Norway , Oman , Pakistan , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Qatar , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Sweden , Switzerland , Taiwan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , Uruguay , Uzbekistan , Viet Nam , Western Sahara , Yemen , Zambia , Zimbabwe

## Output

Output Power Capacity	15.0 KW / 15.0 kVA
Max Configurable Power (Watts)	15.0 KW / 15.0 kVA
Nominal Output Voltage	400 3PH
Output Voltage Distortion	Less than 3%
Output Frequency (sync to mains)	50 Hz , 60 Hz
Other Output Voltages	380, 415V
Other Output Voltages	Double Conversion Online
Output Voltage Tolerance	+/- 1.5%
Output Voltage THD	< 3% linear load

## Input

Nominal Input Voltage	400 3PH
Input Frequency	45 - 65 Hz
Input voltage range for main operations	304 - 477 V
Other Input Voltages	380 , 415
Maximum Input Current	28 A
Input Total Harmonic Distortion	Less than 3% for full load

## Batteries & Runtime

Battery Type	VRLA
Included Battery Modules	2
Battery Slots Empty	1
Replacement battery cartridge note	UPS weight does not include battery weight.
Nominal Battery Voltage	240V

## Communications & Management

Interface Port(s)	E3S_Parallel , E3S_TempSensor
-------------------	-------------------------------

## Physical

Maximum Height	1400.0 mm
Maximum Width	380.0 mm
Maximum Depth	928.0 mm
Net Weight	436.0 kg
Shipping Weight	481.0 kg
Shipping Height	1640.0 mm
Shipping Width	563.0 mm
Shipping Depth	1014.0 mm
Color	White

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-999,9 meters
Storage Temperature	-15 - 40 °C
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	60.000 dB
Online Thermal Dissipation	852.000 BTU/hr
Protection Class	IP 20

## Conformance

Approvals	CE , EAC , IEC 62040-1-1 , IEC 62040-2 , IEC 62040-3 , IEC 62040-4 , ISTA 2B , RCM , WEEE
Standard warranty	1 year on-site repair or replace with factory authorized Start-Up

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs