

# Product data sheet

Specifications



## 13A 250V 1G DP Sw Socket with Neon and Dual Earth Terminal, White

E8215DN\_WE

### Main

Product Or Component Type	Power socket-outlet
Switch Function	Switch
Rated Current	13 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Load Type	Resistive
Cover Frame Colour Tint	White

### Complementary

Wiring Device Mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 2 x 4 mm² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	26.4 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	MS 589-2 BS 1363-2 SS 145-2

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications