

Product data sheet

Specifications



10A 250V 1G Sw 2 Uni Pin + 3 Flat Pin China Skt with Neon, Lavendar Silver

E8215_10USN_LS

! Discontinued

! Discontinued on: Oct 29, 2018

! End-of-service on: Nov 19, 2018

Main

Product Or Component Type	Power socket-outlet
Switch Function	Switch
Rated Current	10 A at 250 V AC 50 Hz
Local Signalling	Neon (amber)
Number Of Gangs	1 gang
Load Type	No inductive load
Cover Frame Colour Tint	Lavender silver

Complementary

Wiring Device Mounting	Surface Flush
Outlet Poles Configuration	2P + E china 2P universal
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Switch: pillar terminals Socket: clamp terminal
Clamping Connection Capacity	2 x 2.5 mm ² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	8.8 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	GB 16915.1-2003 GB 2099.1-2008

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	107 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)