

Product data sheet

Specifications



10A 250V 1G Bel SW w Illu "Pvc",
"Pls CleanUp" & "Pls Wait" Sym,
White

E8231BPDMW_WE

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Control switch Bell switch
Load Type	Fluorescent Resistive
Cover Frame Colour Tint	White

Complementary

Wiring Device Mounting	Surface Flush
Device Mounting	Flush Surface
Switch Function	Switch
Rated Current	10 A at 250 V AC 50 Hz
Local Signalling	Please wait, neon (orange) Please clean up, neon (green) Privacy, neon (red)
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	By screw
Clamping Connection Capacity	1 x 2.5 mm ² for solid cable(s) 1 x 1.5 mm ² for stranded cable(s)
Embedding Depth	21 mm
Width	87 mm
Height	87 mm
Depth	35.5 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	IEC 60669-1 GB 16915.1 SS 227-1 BS EN 60669-1 MS IEC 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	111 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	6 cm
Package 2 Weight	667 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6670.2 g

Contractual warranty

Warranty	18 months
----------	-----------