

Product data sheet

Specifications



16AX 250V 1 Gang 1 Way Switch with Neon, Lavendar Silver

E8231L1N_LS

⚠ Discontinued on: Jul 20, 2017

⚠ End-of-service on: Dec 15, 2017

⚠ Discontinued

Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Switch
Load Type	Fluorescent Resistive
Cover Frame Colour Tint	Lavender silver

Complementary

Device Mounting	Flush Surface
Wiring Device Mounting	Flush Surface
Switch Function	1-way
Rated Current	16 AX at 250 V AC 50 Hz
Local Signalling	Neon
Number Of Gangs	1 gang
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)
Embedding Depth	23 mm
Width	87 mm
Height	87 mm
Depth	35.5 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	IEC 60669-1 GB 16915.1 SS 227-1 BS EN 60669-1 MS IEC 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.55 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	92.538 g

Contractual warranty

Warranty	18 months
----------	-----------