

Product data sheet

Specifications



10A 250V 1 Gang 2 Universal Pin + 3 Flat Pin China Socket, White

E82426_10US_WE

⚠ Discontinued on: Jul 20, 2017

⚠ End-of-service on: Dec 15, 2017

⚠ Discontinued

Main

Product Or Component Type	Power socket-outlet
Switch Function	Unswitch
Rated Current	10 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Load Type	No inductive load
Cover Frame Colour Tint	White

Complementary

Wiring Device Mounting	Surface Flush
Outlet Poles Configuration	2P + E china 2P universal
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Switch: pillar terminals
Clamping Connection Capacity	2 x 2.5 mm² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	8.8 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	GB 2099.1-2008 GB 16915.1-2003

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications