

Product data sheet

Specifications



15A 250V 1 Gang 3 Round Pin Socket, White

E82426_15_WE

⚠ Discontinued on: Feb 17, 2017

⚠ Discontinued

Main

Product Or Component Type	Power socket-outlet
Switch Function	Unswitch
Rated Current	15 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Load Type	Resistive
Cover Frame Colour Tint	White

Complementary

Wiring Device Mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	31.8 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS 546

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.25 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	96 g

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months