



Main

Product or component type	Power socket-outlet
Switch function	Unswitch
Rated current	16 A, 250 V, , AC, 50 Hz
Number of gangs	1 gang
Load type	Resistive
Cover frame colour tint	White

Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate with grid plate Polycarbonate with surround
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 2 x 4 mm ² for stranded cable(s)
Width	87 mm
Height	87 mm
Depth	39 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 60884-1

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications