

Product data sheet

Specifications



16A 250V 1 Gang Schuko Socket, White

E82426_16S_WE

Main

Product Or Component Type	Power socket-outlet
Switch Function	Unswitch
Rated Current	16 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Load Type	Resistive
Cover Frame Colour Tint	White

Complementary

Wiring Device Mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	39 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	IEC 60884-1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications