

# Product data sheet

Specifications



## 45A 250V Double Pole Sw with Neon + 13A Sw Socket with Neon, Lavendar Silver

E82T15D45N\_LS

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range	Pieno
Product Or Component Type	Cooker control unit socket
Switch Application	Switch
Load Type	Fluorescent Resistive
Cover Frame Colour Tint	Lavender silver

### Complementary

Device Mounting	Surface Flush
Wiring Device Mounting	Surface Flush
Rated Current	45 A at 250 V AC 50 Hz
Local Signalling	Neon
Number Of Gangs	1 gang
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Folded terminal Pillar terminals
Clamping Connection Capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 10 mm <sup>2</sup> for stranded cable(s)
Embedding Depth	24.5 mm
Width	147 mm
Height	87 mm
Depth	34.1 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS 4177

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	3.41 cm
Package 1 Width	8.7 cm
Package 1 Length	14.7 cm
Package 1 Weight	251.27 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.256 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	11140.5 g

## Contractual warranty

Warranty	18 months
----------	-----------