

Product data sheet

Specifications



13A 250V Twin Gang Socket, Lavendar Silver

E82T426_LS

⚠ Discontinued on: Feb 17, 2017

⚠ Discontinued

Main

Product Or Component Type	Power socket-outlet
Switch Function	Unswitch
Rated Current	13 A at 250 V AC 50...60 Hz
Number Of Gangs	2 gangs
Load Type	Resistive
Cover Frame Colour Tint	Lavender silver

Complementary

Wiring Device Mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)
Width	147 mm
Height	87 mm
Depth	25.3 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS 1363-2 SS 145-2 MS 589-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.53 cm
Package 1 Width	8.7 cm
Package 1 Length	14.7 cm
Package 1 Weight	122 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------