



Main

Range	AvatarOn
Product or component type	Cover plate
Accessory / separate part category	Mounting accessory
Colour tint	White (painted)
Type of packing	Flow-pack

Complementary

Range compatibility	AvatarOn switched socket
Product destination	Switched socket
Socket number	1
Number of rocker	1
[In] rated current	13 A
Outlet poles configuration	3P
Outlet standard	British BS 1363A
Material	PC (polycarbonate)
Surface finish	Glossy
Surface treatment	Untreated
Height	86 mm
Width	86 mm
Depth	21 mm

Environment

Ambient air temperature for storage	-5...45 °C
Ambient air temperature for operation	0...95 °C
Standards	BS 5733 IEC 60670

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications