



Main

Range	AvatarOn
Product or component type	Switched socket
Device application	Power supply
Device presentation	Complete product
Outlet poles configuration	3P with shutter
Colour tint	White
Type of packing	Flow-pack

Complementary

Rated current	13 A, connector type: socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	1
Outlet standard description	With earthing contact
Outlet standard	China
Pilot light	LED
Service life in cycles	20000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screw terminal
Material	Polycarbonate for grid plate Polycarbonate for surround
Surface finish	Glossy
Surface treatment	Painted mechanism cover
Device mounting	Surface
Fixing mode	Screw
Height	86 mm
Width	86 mm
Depth	31.7 mm

Environment

IP degree of protection	IP20
Ambient air temperature for operation	-5...45 °C

Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Standards	MS 589 BS 1363 SS 145
Product certifications	SIRIM