



Main

Range	AvatarOn
Product or component type	Time delay switch
Device presentation	Mechanism

Complementary

Device mounting	Flush Surface
Number of modules	1 module with 35 x 16 mm
Number of rocker	1
Actuator	Rocker
Fixing mode	Clip-in
Colour tint	White
Surface finish	Glossy
Quantity per set	Set of 1
[Ie] rated operational current	4 A 4 A
[Ue] rated operational voltage	250 V AC 50...60 Hz
Clamping connection capacity	1...4 mm ² (rigid) 1...4 mm ² (stranded) 1...4 mm ² (flexible)
Wire stripping length	12 mm
Material	PC (polycarbonate) for grid plate PC (polycarbonate) for surround PC (polycarbonate) for base PC (polycarbonate) for base cover PC (polycarbonate) for dolly Brass for terminal cover
Height	86 mm
Width	86 mm
Depth	34 mm
Embedding depth	25 mm

Environment

IP degree of protection	IP20
-------------------------	------