

# Product data sheet

Specifications



## Dimmer, AvatarOn, rotary push type, 250 VA, Wine Gold

E8331RD250\_WG\_G11

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Product Or Component Type	Dimmer
Device Presentation	Complete product
Provided Equipment	Screws
Dimmer Application	Ohmic load Capacitive load Inductive load
Dimmer Control	Rotary push type
Load Type	Incandescent lamps - 50...250 W - 220...240 V AC High voltage halogen lamp - 50...250 W - 220...240 V AC Electronic transformer - 50...250 VA Dimmable LED - 3...100 W
Type Of Packing	Carton
Quantity Per Set	Set of 8
Market Segment	Small commercial Residential
Colour Tint	Wine gold
Main Colour Tint	Wine gold

### Complementary

[Ue] Rated Operational Voltage	220...240 V AC 50/60 Hz
Protection Type	Thermal fuse Surge arrester
Actuator	Knob
Fixing Mode	By screws
Clamping Connection Capacity	<= 2 x 2.5 mm <sup>2</sup> for flexible cable(s) <= 2 x 2.5 mm <sup>2</sup> for rigid cable(s)
Wire Stripping Length	12 mm
Material	Polycarbonate: plastic part Brass: terminals Steel coated with zinc chromate: terminal screw
Device Mounting	Flush
Embedding Depth	35 mm

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	0...60 °C
Relative Humidity	10...95 %
Environmental Characteristic	Oil and vapour resistant
Standards	IEC 60669-2-1 CE

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.63 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	125.6 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.104 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	48
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	7128.8 g

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>