

Product data sheet

Specifications



AvatarOn, data socket, RJ45, cat6e, shuttered, White

E8331RJS6_WE_G11

Main

Product Or Component Type	Data socket
Device Application	Communication
Socket Additional Information	Shuttered
Communication Network Category	Data: 6e
Number Of Gangs	1 gang
Colour Tint	White
Main Colour Tint	White

Complementary

Device Presentation	Complete product
Device Mounting	Flush Surface
Data Socket Type	RJ45
Rated Current	1.5 A
Material	Polycarbonate: plastic part
Contacts Material	Housing: PC Contact: phosphor bronze with gold plating
Contact Resistance	1 µOhm
Insulation Resistance	>= 200 MOhm
Minimum Return Loss	23 dB
Colour Tint	White
Ip Degree Of Protection	IP20
Width	86 mm
Height	86 mm
Depth	31 mm

Environment

Dielectric Strength	1000 V for 60 s at 60 Hz
Awg Gauge	AWG 26...AWG 22 (4 twisted pair cables)
Environmental Characteristic	No UV resistant
Maximum Ambient Air Temperature For Operation	35 °C
Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	TIA/EIA-568-B.2-1 ASTMD4566-98
-----------	-----------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	55.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	555.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations