



### Main

Range	AvatarOn
Product or component type	Switch
Device application	Control
Load type	Incandescent lamp Fluorescent lamps Small motor load Resistive Serial boost load (SBL)
Colour tint	Metal gold hairline

### Complementary

Rated current	20 A 250 V AC 50/60 Hz
Switch function	2-pole
Number of rocker	2
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 4 mm <sup>2</sup> for stranded cable(s) 1 x 6 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Brass terminal
Local signalling	LED indicator LED amber on
Material	Polycarbonate + GF 20 % actuator Polycarbonate frame Polycarbonate base Polycarbonate dolly Polycarbonate grid plate
Device mounting	Flush
Width	86 mm
Height	86 mm
Depth	32 mm

### Environment

Ambient air temperature for operation	<= 45 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000

---

Standards	IEC 60669-1 BS EN 60669-1 MS IEC 60669-1 SS 227-1
-----------	--

---