

Product data sheet

Specifications



Telephone socket, AvatarOn, wine gold

E8332RJS4_WG_C5

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Product Or Component Type	Telephone socket
Device Application	Communication
Socket Additional Information	Shuttered
Number Of Gangs	2 gangs
Material	PC (polycarbonate): housing Polycarbonate: plastic part
Colour Tint	Wine gold
Colour Tint	Wine gold

Complementary

Device Presentation	Complete product
Device Mounting	Surface Flush
Communication Network Category	Voice: 3
Rated Current	1.5 A
Contacts Material	Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Contact Resistance	1 µOhm
Insulation Resistance	>= 200 MOhm
Minimum Return Loss	23 dB
Width	86 mm
Height	86 mm
Depth	40.7 mm

Environment

Dielectric Strength	1000 V for 60 s at 60 Hz
Awg Gauge	AWG 26...AWG 22 (4 twisted pair cables)
Environmental Characteristic	UV resistant
Maximum Ambient Air Temperature For Operation	45 °C
Standards	TIA/EIA-568-B.2-1 ASTMD4566-98
Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	68.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	748.0 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations