



Main

Range	AvatarOn
Product or component type	USB charger
Mounting mode	Fixed
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.1 A

Complementary

Device mounting	Surface
Device presentation	Mechanism
Colour tint	White
Surface finish	Glossy
Number of modules	1 module
Connector type	USB 2.1
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Maximum load current with 2 outputs used simultaneously	2.1 A
Material	PC (polycarbonate) for base
Connections - terminals	Screw terminals
Screwdriver shape	Phillips combined
Clamping connection capacity	1.5...2.5 mm ² (rigid) 1.5...2.5 mm ² (flexible)
Height	86 mm
Width	86 mm
Depth	40 mm

Environment

Standards	IEC 60950-1
-----------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.