



Main

Range	AvatarOn
Product or component type	Cover plate
Accessory / separate part category	Mounting accessory
Cover type	Key holder
Colour tint	Wine gold painted
Type of packing	Flow-pack

Complementary

Range compatibility	switch
Product destination	Switch
Number of rocker	3
Material	PC (polycarbonate)
Surface finish	Glossy
Surface treatment	Untreated
Height	86 mm
Width	96 mm
Depth	21 mm

Environment

Ambient air temperature for storage	-5...45 °C
Ambient air temperature for operation	0...95 °C
Standards	IEC 60670 BS 5733

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations