

Product data sheet

Specifications



3 Switch, AvatarOn, 1-pole 1-way, LED, brass terminal, IP20, wood

E8333L1LED_WD_C5

Main

Product Or Component Type	Switch
Device Application	Control
Load Type	Fluorescent lamp Inductive Incandescent lamp Resistive
Colour Tint	Wood

Complementary

Device Presentation	Complete product
Rated Current	16 AX at 250 V AC 50/60 Hz
Switch Function	1-pole 1-way
Number Of Gangs	3 gangs
Number Of Rocker	3
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - Terminals	Brass terminal
Local Signalling	Off: LED indicator, LED (amber)
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator
Device Mounting	Flush Surface
Width	86 mm
Height	86 mm
Depth	34.2 mm

Environment

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	45 °C
Operating Altitude	2000 m
Relative Humidity	0...95 %
Environmental Characteristic	UV resistant

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60669-1 MS IEC 60669-1 BS EN 60669-1 SS 227-1
-----------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	106.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1168.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations