



Main

Range	AvatarOn
Product or component type	Switch
Device application	Control
Load type	Fluorescent lamp Incandescent lamp Inductive Resistive
Colour tint	Metal gold hairline

Complementary

Rated current	16 A 250 V AC 50/60 Hz
Switch function	1-way
Number of gangs	4 gangs
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Brass terminal
Local signalling	LED indicator LED amber off
Material	Polycarbonate + GF 20 % actuator Polycarbonate frame Polycarbonate base Polycarbonate dolly Polycarbonate grid plate
Device mounting	Flush Surface
Width	86 mm
Height	86 mm
Depth	34.2 mm

Environment

Ambient air temperature for operation	<= 45 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant

Operating altitude	2000
Standards	BS EN 60669-1 IEC 60669-1 MS IEC 60669-1 SS 227-1
