



Main

Range	AvatarOn
Product or component type	Socket-outlet
Device application	Power supply
Load type	No inductive load
Colour tint	Wood
Socket additional information	Shuttered

Complementary

Rated current	13 A 250 V AC 50 Hz
Number of gangs	1 gang
Outlet poles configuration	3P with shutters China
Clamping connection capacity	1 x 4...2 x 4 mm ² for solid cable(s) 1 x 4...2 x 4 mm ² for stranded cable(s) 1 x 2.5...3 x 2.5 mm ² for solid cable(s) 1 x 2.5...3 x 2.5 mm ² for stranded cable(s)
Connections - terminals	Folded terminal
Material	Polycarbonate cover Polycarbonate grid plate Polycarbonate surround
Device mounting	Surface
Width	86 mm
Height	86 mm
Depth	27.8 mm

Environment

IP degree of protection	IP20
Ambient air temperature for operation	<= 45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Standards	SS 145 MS 589 BS 1363

