



### Main

Range	AvatarOn
Product or component type	Socket-outlet
Device application	Power supply
Load type	No inductive load
Colour tint	Wood
Socket additional information	Shuttered

### Complementary

Rated current	13 A 250 V AC 50 Hz
Number of gangs	1 gang
Outlet poles configuration	3P with shutters China
Clamping connection capacity	1 x 4...2 x 4 mm <sup>2</sup> for solid cable(s) 1 x 4...2 x 4 mm <sup>2</sup> for stranded cable(s) 1 x 2.5...3 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 2.5...3 x 2.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Folded terminal
Material	Polycarbonate cover Polycarbonate grid plate Polycarbonate surround
Device mounting	Surface
Width	86 mm
Height	86 mm
Depth	27.8 mm

### Environment

IP degree of protection	IP20
Ambient air temperature for operation	<= 45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Standards	BS 1363 MS 589 SS 145

