

Product data sheet

Specifications



Switched socket, AvatarOn, LED,
screw terminal, IP20, white

E83T25N_WE_G11

Main

Product Or Component Type	Switched socket
Device Application	Power supply
Device Presentation	Complete product
Outlet Poles Configuration	3P with shutter
Type Of Packing	Flow-pack

Complementary

Rated Current	13 A socket-outlet
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Socket Number	2
Outlet Standard Description	With earthing contact
Outlet Standard	British BS 1363A
Number Of Gangs	2 gangs
Pilot Light	LED
Service Life In Cycles	20000 cycles
Electrical Durability	5000 cycles
Connections - Terminals	Screw terminal
Material	Polycarbonate: grid plate Polycarbonate: surround
Surface Finish	Glossy
Surface Treatment	Painted mechanism cover
Device Mounting	Surface
Fixing Mode	Screw
Height	86 mm
Width	146 mm
Depth	31.7 mm

Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...45 °C
Ambient Air Temperature For Storage	-5...60 °C
Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	
	SS 145
	MS 589
	BS 1363
Product Certifications	SIRIM

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	14.6 cm
Package 1 Weight	152 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	7
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.121 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	42
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	7847 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations