



Main

Range	AvatarOn
Product or component type	Shaver socket
Installation direction	Vertical
Input voltage	240 V, AC, 50/60 Hz
Output voltage	115 V, AC, 50/60 Hz 240 V, AC, 50/60 Hz
Material	Polycarbonate, for grid plate Polycarbonate, for surround Brass, for terminals Polycarbonate, for bracket
Colour tint	White

Complementary

Device mounting	Flush Surface
Cable cross section	1...2.5 mm ²
Rated operational power in VA	20 VA
Connections - terminals	Pillar terminals
Width	86 mm
Height	147 mm
Depth	50 mm

Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000 m
IP degree of protection	IP21
Standards	IEC 61558-2-5