

# Product data sheet

Specifications



## 10A 1 Gang 3 Flat Pin Switched Socket with Shutter and Ondicator, Silver White

E8415-10S\_SW

! Discontinued

! Discontinued on: Sep 30, 2020

! End-of-service on: Oct 26, 2020

### Main

Product Or Component Type	Power socket-outlet
Socket Additional Information	Shuttered
Outlet Poles Configuration	2P + E China
Load Type	Resistive
Cover Frame Colour Tint	Silver white
Cover Plate Colour Tint	White

### Complementary

Device Mounting	Surface Flush
Local Signalling	Mechanical indicator
Switch Function	Push-button
Rated Current	10 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround
Connections - Terminals	Brass pillar Clamps terminal
Embedding Depth	23.8 mm
Width	87 mm
Height	87 mm
Depth	32 mm

### Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	GB 2099.1 GB 16915.1
Standards	GB 2099.1 GB 16915.1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------