

Product data sheet

Specifications



10A 1 Gang 3 Flat Pin Switched Socket with Shutter and Ondicator, Silver Bronze

E8415-10S_SZ

Main

Product Or Component Type	Power socket-outlet
Socket Additional Information	Shuttered
Outlet Poles Configuration	2P + E China
Load Type	Resistive
Cover Frame Colour Tint	Silver bronze
Cover Plate Colour Tint	Bronze

Complementary

Device Mounting	Flush Surface
Local Signalling	Mechanical indicator
Switch Function	Push-button
Rated Current	10 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround
Connections - Terminals	Clamps terminal Brass pillar
Embedding Depth	23.8 mm
Width	87 mm
Height	87 mm
Depth	32 mm

Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	GB 2099.1 GB 16915.1
Standards	GB 16915.1 GB 2099.1

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

Contractual warranty

Warranty	18 months
----------	-----------