

# Product data sheet

Specifications



## 15A 1 Gang 3 Round Pin Switched Socket with Shutter and Ondicator, Silver Satin

E8415-15\_SA

### Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	2P + E
Load Type	No inductive load
Cover Frame Colour Tint	Silver satin
Cover Plate Colour Tint	Grey

### Complementary

Device Mounting	Surface Flush
Local Signalling	On: mechanical indicator (amber) Off: mechanical indicator (silver satin)
Rated Current	15 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Polycarbonate base Polycarbonate grid plate Polycarbonate surround
Connections - Terminals	Folded terminal
Width	87 mm
Height	87 mm
Depth	8 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	BS 546 MS 1577 SS 472
Standards	SS 472 MS 1577 BS 546

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications