

Product data sheet

Specifications



13A 1 Gang Double Pole Switched Socket with Ondicator, Silver Satin

E8415D_SA

⚠ Discontinued on: Feb 17, 2017

⚠ Discontinued

Main

| | |
|---------------------------|---------------------|
| Product Or Component Type | Power socket-outlet |
| Load Type | Resistive |
| Cover Frame Colour Tint | Silver satin |
| Cover Plate Colour Tint | Grey |

Complementary

| | |
|-------------------------|---|
| Device Mounting | Surface Flush |
| Local Signalling | Mechanical indicator (amber) |
| Switch Function | 2-pole |
| Rated Current | 13 A at 250 V AC 50 Hz |
| Number Of Gangs | 1 gang |
| Material | Brass contact Phosphor contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround |
| Connections - Terminals | Folded terminal |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 8 mm |

Environment

| | |
|---------------------------------------|-------------------------------|
| Ambient Air Temperature For Operation | -5...40 °C |
| Relative Humidity | 0...95 % |
| Environmental Characteristic | UV resistant indoor use |
| Operating Altitude | 2000 m |
| Standards | BS 1363-2 MS 589 SS 145 |
| Standards | BS 1363-2 MS 589 SS 145 |

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 8.72 cm |
| Package 1 Length | 8.72 cm |
| Package 1 Weight | 119.517 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|