



Main

Range	ZENcelo
Product or component type	Power socket-outlet
Socket additional information	Shuttered
Outlet poles configuration	2P + E china
Load type	Resistive
Colour tint	Black
Cover frame colour tint	White

Complementary

Device mounting	Flush Surface
Local signalling	Mechanical indicator
Switch function	Push-button
Rated current	10 A 250 V AC 50 Hz
Number of gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Brass pillar Clamps terminal
Embedding depth	23.8 mm
Width	87 mm
Height	87 mm
Depth	32 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant

Operating altitude	2000 m
Standards	GB 16915.1 GB 2099.1
Standards	GB 16915.1 GB 2099.1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations