

Product data sheet

Specifications



ZENcelo - 10A 250V - 1 gang 2 universal pin + 3 flat pin switched socket (SW)

E8415_10USR_SW_C1

⚠ Discontinued on: May 24, 2017

⚠ Discontinued

Main

Range Of Product	ZENcelo
Product Or Component Type	Power socket-outlet
Local Signalling	Mechanical indicator (red)
Rated Current	10 A at 250 V AC 50 Hz
Cover Frame Colour Tint	Silver white
Cover Plate Colour Tint	White

Complementary

Device Mounting	Surface Flush
Socket Additional Information	Shuttered
Outlet Poles Configuration	2P + E China 2P universal
Clamping Connection Capacity	1 x 4...2 x 4 mm ² for solid cable(s) 1 x 4...2 x 4 mm ² for stranded cable(s) 1 x 2.5...3 x 2.5 mm ² for solid cable(s) 1 x 2.5...3 x 2.5 mm ² for stranded cable(s)
Number Of Gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround
Load Type	Resistive
Connections - Terminals	Clamps terminal
Embedding Depth	20.1 mm
Width	87 mm
Height	87 mm
Depth	27 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	GB 16915.1 GB 2099.1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

