

Product data sheet

Specifications



1 Gang Fused Connection Unit with Neon, Silver White

E8430FSGN_SW

⚠ Discontinued on: Mar 29, 2013

⚠ Discontinued

Main

Product Or Component Type	Fused connection unit
Rated Current	13 A at 250 V AC 50 Hz
Material	Polycarbonate: base Polycarbonate: grid plate Polycarbonate: surround
Local Signalling	Indicator light neon
Cover Frame Colour Tint	Silver white

Complementary

Wiring Device Mounting	Surface Flush
Number Of Gangs	1 gang
Number Of Cables	2 - cable cross section: 4 mm ² input 1 - cable cross section: 1.5 mm ² output 1 - cable cross section: 2.5 mm ² output 3 - cable cross section: 2.5 mm ² input 3 - cable cross section: 0.5...1.5 mm ²
Contacts Material	Contact: brass and phosphor bronze
Load Type	Resistive
Connections - Terminals	Folded terminal
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	BS 1362-4

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications